



The piloted vacuum valve CSP series mounts directly on the suction cup and allows to maintain the vacuum in it, in case of emergency stop or malfuntioning of the vacuum generator.

The controlled dropping is done by connecting the fitting attached to the compressed air.

Note: The empty valve is not a positive safety feature. Regular maintenance is needed to ensure the proper functioning of the valve.

Materials


Valve	Nitrile (NBR)				
Body	Anodized aluminum				

Filter Stainless steel screen 200 µ

Characteristics								
Reference	ØG	ØG1	D	F	L	J	E 💊	
CSP 14	G1/4"-F	G1/4"-M	4x6	25	33	12.8	21	




4



To the vacuum generator

Mounting

- One piloted vacuum valve by suction cup.
- Blow-off pressure, minimum 5 bar.





Please specify the part e.g.: CSP14 See part n° table above.

Note: All dimensions are in mm

